

Technical data	MFA 20
Accuracy class EN ISO 9513	0.5
Measuring principle	Strain gauge
Travel for tensile testing	+ 20 mm
Measuring path tolerance	50 µm
Measuring path tolerance	0.25 %
Linearity error including hysteresis	0.2 %
Indication error (rel.)*	0.5 %
Indication error*	1.5 µm
Error in gauge length (L _e)	0.5 %
Activating force	150 cN
Standard gauge length (L _e)	50 – 100 mm (steps of 10 (5) mm)
Option: gauge length (L _e)	from 40 mm
Accessory: gauge length (L _e)	up to 200 mm (steps of 10 (5) mm)
Weight	ca. 480 g

* The larger value is admissible

Adjustable at sample cross section


round	Ø 4 to 30 mm
flat	15 x 1 to 30 x 30 mm
with special clamping device	Ø 4 up to 60 mm
with special clamping device	60 mm thickness and 60 mm width
Cable length	5 m

Strain gauge

Sensitivity	1 mV/V
Rated resistance of bridge	350 Ω
Voltage input	5 V

MFA 20

Hand clamped extensometer



M e s s - & F e i n w e r k t e c h n i k G m b H



P r e c i s i o n t e s t i n g o f l i n e a r s t r a i n

Area of application

The clip-on extensometer MFA 20 is suitable for determination of the yield point and uniform deformation of test samples above 4 mm diameter and 15 mm width. The measurement accuracy corresponds to the accuracy class 0.5 of the EN ISO 9513. Because of its extremely robust design the instrument is suited for heavy duty application such as testing of construction steel and rough samples with scale etc. The gauge length can be adjusted very quickly and precisely from 50 to 200 mm in 10 (5) mm-steps by shifting the lower knife edge holder. The attachment can be done without any problems with one hand. The parallel positioning of the MFA 20 in respect to the axis of round samples is guaranteed by centering between the two double knife edges (see top view of the drawing).

Design and function

The MFA 20 consists of two casing halves which moves parallel and easily towards each other on play-free guidance bars. The upper casing overlaps the lower casing for the total extension so that the parallel guide and the measuring system are protected from damage and dust. A measuring spring with a temperature-compensated full bridge strain gauge serves as the measuring system for the MFA 20. The knife edge holders and the clamping device can be positioned easily by loosening just one knurled screw. Alignment pins fix them in their exact position.

In order to achieve a symmetrical position of the counter rollers with respect to the knife edges, the counter roller fixture can be turned and the clamping device shifted in three steps. The initial gauge length can be adjusted up to 140 mm with the upper extension arm and up to 200 mm with both the upper and lower extension arms in steps of 10 mm. Even intermediate lengths like e.g. 55 to 195 mm may be obtained by additional shifting of the upper and lower knife edges (see diagram). The clamping device is compatible to that of the MFA 2/05.

Opening width and clamping force are continually adjustable. For initial

gauge lengths greater than 100 mm the holder which belongs to the extension arm and has the greater distance between the counter rollers must be used.

The casing is made of a high strength aluminium alloy and has a long lasting and scratch-resistant hard anodized surface. For the small parts argent tan and stainless steel are used. The round knife edges can be utilized along the entire perimeter by rotating them. Thereby a longer lifetime is achieved.

Operation

For clamping the MFA 20 open the clamping device with thumb and fore finger. While mounting care has to be taken that the lower knife edges are placed on the sample first. The measurement can be started then. No unlocking or adjustments have to be made to operate the MFA 20.

Recommendation

If the L_e has to be changed very often to intermediate lengths an additional set of knife edge holders may be useful and time-saving. The calibration instrument KMF 100 is suitable for linearity checks.

Spare parts and accessories

Special clamping device for samples of 60 mm width and 60 mm thickness

Extension arm (upper) up to $L_e = 140$ mm** and fixture with larger counter roller distance

Extension arm (lower) up to $L_e = 160$ mm** and fixture with larger counter roller distance

Spare fastening screw M3 x 8 T10 for knife edge and extension arm

Spare knife edge, $\varnothing 9$ mm

Knife edge holder (upper) with knife edges


Knife edge holder (lower) with knife edges

* depending on version


** With both extension arms a L_e of up to 200 mm can be achieved.

Delivery scope

- | | |
|---|---|
| 1 | MFA 20, L_e from 50 mm to 100 mm |
| 1 | MFA 20 clamping device with cylindrical counter rollers |
| 1 | Knife edge holder (upper) |
| 1 | Knife edge holder (lower) |
| | cable (5 m) |
| 2 | Spare fastening screws M3 x 8 T10 |
| | screw driver TORX T10 |
| 1 | Test report |
| 1 | Storing case |



Picture 1: Connecting diagram: Strain gauge full bridge



Picture 2: MFA 20 - Dimensions